



AMERICAN ACCENTS METALLIC LEAFING PENS

DESCRIPTION AND USES

Rust-Oleum® American Accents® Metallic Leafing Pens are designed to decorate and personalize items around the home such as picture frames, candy jars, vases, storage bins, greeting cards, candle holders and more. Use on wood, metal, glass, unglazed ceramic, paperboard and some plastics. The Metallic Leafing Pen is suitable for used outdoors on mailboxes, planters and birdhouses.

PERFORMANCE CHARACTERISTICS

- Easy to use with excellent coverage
- Rich satin finish
- Durable and permanent
- Special chisel tip for broad or narrow lines
- Dries to the touch in 15-30 minutes

PRODUCTS

SKU (1/3 fl. oz.)	Description
215190	Gold Leafing Pen
215191	Silver Leafing Pen
215192	Copper Leafing Pen

PRODUCT APPLICATION

PAINTING CONDITIONS

Apply only when air and surface temperatures are above 50-90°F (10-32°C) and humidity is below 85% to ensure proper drying.

DIRECTIONS

Hold cap in place and shake paint pen for 30 seconds. Twist and remove cap. Lightly depress tip several times on scrap paper to start paint flow. Recap and shake as needed. When finished, replace cap tightly and store on side.

DRY & RECOAT TIMES

Dry and recoat times are based on 70°F and 50% relative humidity. Allow more time at cooler temperatures. Dries to touch in 15-30 minutes, dry to handle in 1 hour, and fully dry in 2-4 hours.

CLEAN-UP

Wipe up spills and excess with mineral spirits.

TECHNICAL DATA

AMERICAN ACCENTS METALLIC LEAFING PENS

PHYSICAL PROPERTIES

		PAINT PEN
Resin Type		Polystyrene
Pigment Type		Varies with color
Solvents		Mineral Spirits
Specific Gravity		1.12
Volatile Organic Compounds		<100 g/l
Recommended Dry Film Thickness (DFT) per Coat		NA
Practical Coverage at Recommended DFT (assumes 15% material loss)		Varies with surface type and porosity
Dry Times at 77°F (25°C) and 50% Relative Humidity	Touch	15-30 minutes
	Handle	1 hour
	Fully Dry	2-4 hours
Shelf Life		3 years
Flash Point		91°F (32°C)
Safety Information		For more information, see MSDS

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.