

Specification Sheet

3PE[™] Particulate Respirator X127, N95

Key Features

- 95% filtration rate
- Adjustable nose clip
- Adjustable head strap

Material Composition

- Straps and strap clip
- Nose Clip
- Filter piece
- This respirator contains no components made from natural rubber latex
- Approximate weight of product: 0.3 oz

Country of Origin

Made in the USA with globally sourced materials

Use For

- Use for solid particulates and liquid mists in concentrations not exceeding 10X PEL/OEL
- Always follow User Instructions and use in manners as indicated

Do Not Use For

- DO NOT use for gases and vapors, oil aerosols, asbestos, arsenic, cadmium, lead, 4,4-methylene dianiline (MDA), or abrasive blasting
- DO NOT use for particulate concentrations exceeding 10X PEL/OEL
- DO NOT use in any manner not indicated in the User Instructions

Approvals and Standards

- NIOSH approved N95 particulate respirator
- Meets NIOSH 42 CFR 84 N95 requirements for a minimum 95% filtration efficiency against solid and liquid aerosols that do not contain oil.

Time Use Limitation

Replace the respirator when it becomes dirty, damaged, or difficult to breathe through.

Shelf Life and Storage

Pacific PPE Corp
2875 S Reservoir St,
Pomona, CA 91766

E-mail: contact@3peco.com

- 5 years from the date of manufacture
- Store respirators in the original packaging, away from contaminated areas, dust, sunlight, extreme temperatures, excessive moisture, and damaging chemicals.
- Store in temperatures between -4°F (-20°C) and +86°F (+30°C) and not exceeding 80% RH