


Size Chart




Small



Medium



Large



Extra Large

PlexiDor Size	Weight of Pet	Breed Size Examples	Type of Installation	Opening for Pet	Installation Cut Hole	Overall Dimensions†
Small SM	Up to 9 lbs (Dog) 24 lbs (Cat)	Cats, Chihuahuas, Pomeranians, Papillons, Yorkies, Maltese and Japanese Chins	Door Series	6½" x 7¼"	8½" x 8½"	10" x 10"
			Wall Series	6½" x 7¼"	8¾" x 10½"†	10" x 12"
Medium MD	Up to 40 lbs	Poodles, Corgis, Dachshunds, Beagles, Pekingese, Shelties, Schnauzers, Cocker Spaniels and most Terriers	Door Series	9" x 12"	11½" x 13½"	13¾" x 15½"
			Wall Series	9" x 12"	11⅞" x 15¼"†	13¾" x 17½"
Large LG	Up to 100 lbs	Labradors, German Shepherds, Golden Retrievers, Boxers, Collies, Setters, Bulldogs, Pointers and Dobermans	Door Series	11¾" x 16"	14¼" x 17¾"	16½" x 19¼"
			Wall Series	11¾" x 16"	14½" x 19"†	16½" x 21¼"
Extra Large XL	Up to 220 lbs	Great Danes, St. Bernards, Rottweiler, Old English Sheepdogs, Newfoundlands, Irish Wolfhounds and Great Pyrenees	Door Series	16" x 23¾"	18" x 25"	20½" x 26¾"
			Wall Series	16" x 23¾"	18½" x 26½"†	20½" x 28¾"
Electronic PDE	Up to 125 lbs	Large breed examples as listed including Malamutes, Weimaraners, Rhodesian Ridgebacks and all Cats	Door Series	12¾" x 20"	14¼" x 21½"	17⅞" x 54⅝"
			Wall Series	12¾" x 20"	14¼" x 23"†	17⅞" x 54⅝"


† Note: There are two dimensions for the Wall Series cut hole, interior and exterior. Read the installation instructions carefully before cutting. ‡ Dimensions listed in chart are Width by Height.

Installation Height


The installation distance from frame to floor.

Installing your PlexiDor Pet Door at the correct height will ensure the door is comfortable for your pet to use. Stepping up and through the door is best.

Important: The suggested measurements are a guide only. Make sure the pet door is installed so that the opening is at least two inches above the pet's back.



Frame Colors



Have questions about the size that's right for your pet? Call us at **800-749-9609**